

REFLEX EXTRA SILVER

SPECIFICATIONS

Composition	± Average Thickness	Q Carrier	& Certifications		
PU	140- 150 microns		REACH n° 1907/2006/EU		
		non adhesive polyester	OEKO-TEX ® COMFIDENCE IN TEXTILES STANDARD 100 19.HIT.86736 HOHENSTEIN HTTI		

APPLICATION INSTRUCTIONS

⊘ Applies on	SUGGESTED CUTTING SETTINGS			TRANSFER SETTINGS			
nylon, polyester, treated fabrics,	Blade	<u></u> Pressure	>> Speed	Time	Temperature	Pressure	Peel
leather	60°	60 gf	20 cm/sec	5+10 seconds	160°C (320°F)	Light	cold

- → Remove the protective film
- → Cut the mirror material
- → Peel off excess material
- → Place the decoration on the fabric
- → Transfer for 5" under the suggested conditions
- → Remove the carrier when cold
- → Cover with Teflon or silicone paper
- → Press another 10" for final fixing

PRODUCT HIGHLIGHTS

→ Applicable on difficult fabrics (nylon, treated fabrics)

 $oldsymbol{\mathcal{L}}$ NOTE: We highly recommend to perform a test before launching a production

CARE AND WASHING RECOMMENDATIONS

Washing	Ironing	Tumble dry	Ony cleaning	Storage Shelf Life	Storage Temperature	Storage Conditions	∮ Position
Up to 40°C, best inside-out	NO	NO	NO	Up to 2 years	Between 18°C and 26°C	Away from sunlight and dust	Vertical

- → Wait 24 hours after the application before the first wash
- → Respect the textile recommendations
- → Do not bleach or use aggressive chemical agents

This document can be subject to variations. Updated versions are available on www.siser.com. For further information, please contact our sales office: info@siser.it



Siser s.r.l. Viale della Tecnica, 18 36100 Vicenza - Italy Tel. +39 0444.287960 Fax +39 0444.287959 info@siser.it www.siser.com r.e.a. vi 171856 reg. imp. vi n° 14971 c.s. € 103.300 i.v. p.iva 01591490246



